




A large industrial heat treatment chamber, the Microtec HeatPRO, is shown. It has a dark grey body with a large glass door on the left side. The Microtec logo and 'heatPRO' branding are visible on the front. A robotic arm with a gripper is mounted on top, and a control panel with a screen and buttons is attached to the side. The background is a blue and white geometric pattern.



DFT

- [illegible]

- 本機は、膜の長さ、幅、厚さを自由に設定でき、膜の厚さを0.1mmから0.5mmまで調整可能。
- 本機は、膜の厚さを自由に設定でき、膜の厚さを0.1mmから0.5mmまで調整可能。
- 本機は、膜の厚さを自由に設定でき、膜の厚さを0.1mmから0.5mmまで調整可能。



仕様

- 膜の長さ、幅、厚さ ≤30x30cm
- 膜の厚さを0.1mmから0.5mmまで調整可能
- 膜の厚さを自由に設定でき、膜の厚さを0.1mmから0.5mmまで調整可能
- 膜の厚さを0.1mmから0.5mmまで調整可能
- 膜の厚さを0.1mmから0.5mmまで調整可能
- 膜の厚さを0.1mmから0.5mmまで調整可能

- 解析度0.4mp-0.6mp
- 解析度120x90x178cm
- 重量245kg

SSE

本製品は、最新のSSE-001を採用し、高品質な画像を出力します。

Microtec 4は、高品質な画像を出力します。Tは、高品質な画像を出力します。

本製品は、最新のSSE-001を採用し、高品質な画像を出力します。

仕様

本製品は、最新のSSE-001を採用し、高品質な画像を出力します。

Microtecは、高品質な画像を出力します。Tは、高品質な画像を出力します。

- 解析度0.4mp-0.6mp
- 2解析度 解析度
- 5解析度 解析度
- 5解析度 解析度
- 6解析度 解析度

本製品は、最新のSSE-001を採用し、高品質な画像を出力します。